

### **PRODUCTS**



Breakthrough design engineering and high performance polymers have enabled Neo Medical to optimize the traditional inventory of 200+ screw sizes and design variations, into **only 14 state of the art screws**, while providing equivalent standard of care treatment options, without the burden of an unnecessarily complex and massive inventory.

Each surgical step has been meticulously optimized, resulting in a simpler procedure with higher efficiency and reduced OR time. The Neo system design transforms today's available typical Instrumentation set of 7 trays, 60 + instruments, weighing up to 70 kg/155 lbs to only 5 instruments, weighing a total of approximately 1kg/2.2 lbs, while preserving the surgical options for the surgeon.



All operating room staff members benefit significantly to the novel instrumentation, primarily through **the simplicity and intuitive nature of the design**, allowing increased focus to meet expectations for optimal clinical outcomes.

## **PRODUCTS**



The unmatched versatility of the Neo Pedicle Screw System™ facilitates any option of reduction, compression, distraction and screw augmentation, for degenerative, tumor or trauma pathologies.



Every detail has been optimized, including the packaging and transportation of the Neo Pedicle Screw System $^{\text{TM}}$ , which is **designed for maximum flexibility**, to contribute to the speed and efficiency of the procedure set up and close.

# Neo Pedicle screw instrument kit

#### **Flexibility**

Single Use & Sterile For MIS and OPEN technique

#### Intuitivity

5 Instruments only Quick Reference Guide

#### Quality

Swiss Quality Instruments Full Traceability



- 1. 4 K-Wires
- 2. Awl for Open Surgery
- 3. Steffee for Open Surgery
- 4. Pedicle Probe
- 5. T-Handle
- 6. Rod Measurer
- **7.** Rod Holder
- 8. Screw Driver
- 9. Counter-Torque Handle
- 10. Option: Screw Extender Remover & Removable Screw Extender

## PEDICLE SCREW KIT

#### **Flexibility**


16 Options per Screw Intra-operative choice of Option

#### Intuitivity

14 References Premounted Implants


#### Quality


Sterile Swiss Implants Full Tracability




- 1. Sterile Pre-Mounted Screws
- 2. Radio transparent Screw Extender
- 3. 2 Sterile premounted Setscrews
- 4. Built-in Torque LImiter
- 5. Built-in Built-in Hardware Removal
- 6. Cannulated Fenestrated Screw
- 7. Continuous Thread in Screw Extender
- 8. Pre-mounted Sleeve
- 9. Pre-mounted 2 Clips for Mono-axial: Locking of Screws
- 10. Visual Marks to identify Key Surgical Steps

The rod kit contains two rods.







## **OPTIONS**



#### **Removal Kit for Revisions**

- 1. Replacable Screw Extender
- 2. 4 Screw Removers
- 3. Counter Torque Handle
- 4. Solid Screw Driver



**Compressor / Distractor Kit** 









**K-wire Kit**Packed in a box of 5 set with 2 pieces per set

## CATALOGUE NUMBERS

Pedicle screw kit 2 x (05.0 x 35 mm)	Description	Arti	Article Number										
Pedicle screw kit 2 x (05.0 x 40 mm)													
Pedicle screw kit 2 x (0/50 x 45 mm)	Pedicle screw kit 2 x (Ø5.0 x 35 mm)	S	С	-	5	0	-	3	5	-	Р	Е	
Pedicle screw kit 2 x (Ø50 x 50 mm)  S C - 5 0 - 5 0 - P E Pedicle screw kit 2 x (Ø6.0 x 40 mm)  S C - 6 0 - 4 0 - P E Pedicle screw kit 2 x (Ø6.0 x 40 mm)  S C - 6 0 - 4 5 - P E Pedicle screw kit 2 x (Ø6.0 x 45 mm)  S C - 6 0 - 4 5 - P E Pedicle screw kit 2 x (Ø6.0 x 45 mm)  S C - 6 0 - 4 5 - P E Pedicle screw kit 2 x (Ø6.0 x 55 mm)  S C - 6 0 - 5 5 0 - P E Pedicle screw kit 2 x (Ø6.0 x 55 mm)  S C - 6 0 - 5 5 5 - P E Pedicle screw kit 2 x (Ø70 x 40 mm)  S C - 6 0 - 5 5 5 - P E Pedicle screw kit 2 x (Ø70 x 40 mm)  S C - 7 0 - 4 0 - P E Pedicle screw kit 2 x (Ø70 x 40 mm)  S C - 7 0 - 4 5 - P E Pedicle screw kit 2 x (Ø70 x 40 mm)  S C - 7 0 - 4 5 - P E Pedicle screw kit 2 x (Ø70 x 45 mm)  S C - 7 0 - 4 5 - P E Pedicle screw kit 2 x (Ø70 x 45 mm)  S C - 7 0 - 4 5 - P E Pedicle screw kit 2 x (Ø70 x 55 mm)  S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2 x (Ø70 x 55 mm)  S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2 x (Ø70 x 55 mm)  S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2 x (Ø70 x 55 mm)  S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2 x (Ø70 x 55 mm)  S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2 x (Ø70 x 55 mm)  S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2 x (Ø70 x 55 mm)  S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2 x (Ø70 x 55 mm)  S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2 x (Ø70 x 55 mm)  S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2 x (Ø70 x 55 mm)  S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2 x (Ø70 x 55 mm)  S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2 x (Ø70 x 55 mm)  S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2 x (Ø70 x 55 mm)  S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2 x (Ø70 x 55 mm)  S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2 x (Ø70 x 55 mm)  S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2 x (Ø70 x 55 mm)  S C - 7 0 0 - 5 5 0 - P E Pedicle screw kit 2 x (Ø70 x 55 mm)  S C - 7 0 0 - 5 5 0 - P E Pedicle screw kit 2 x (Ø70 x 55 mm)  S C - 7 0 0 - 5 5 0 - P E Pedicle screw kit 2 x (Ø70 x 55 mm)  S C - 7 0 0 - 5 5 0 - P E Pedicle screw kit 2 x (Ø70 x 55 mm)  S C - 7 0 0 - 5 5 0 - P E Pedicle screw kit 2 x (Ø70 x 55 mm)	Pedicle screw kit 2x (Ø5.0 x 40 mm)	S	С	-	5	0	-	4	0	-	Р	Е	
Pedicle screw kit 2x (26.0 x 35 mm) S C - 6 0 - 3 5 - P E Pedicle screw kit 2x (26.0 x 40 mm) S C - 6 0 0 - 4 0 0 - P E Pedicle screw kit 2x (26.0 x 45 mm) S C - 6 0 0 - 4 5 - P E Pedicle screw kit 2x (26.0 x 50 mm) S C - 6 0 - 5 5 0 - P E Pedicle screw kit 2x (26.0 x 55 mm) S C - 6 0 - 5 5 0 - P E Pedicle screw kit 2x (27.0 x 35 mm) S C - 6 0 - 5 5 5 - P E Pedicle screw kit 2x (27.0 x 40 mm) S C - 7 0 - 4 0 - P E Pedicle screw kit 2x (27.0 x 40 mm) S C - 7 0 - 4 5 - P E Pedicle screw kit 2x (27.0 x 40 mm) S C - 7 0 - 4 5 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 4 5 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 4 5 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 5 5 5 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 5 5 5 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 5 5 5 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 5 5 5 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 5 5 5 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 5 5 5 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 5 5 5 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 5 5 5 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 4 5 5 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 4 5 5 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 4 5 5 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 4 5 5 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2x (27.0 x 50 mm) S C - 7 0 - 7 0 - 7 0 - P B Pedicle scre	Pedicle screw kit 2 x (Ø5.0 x 45 mm)	S	С	-	5	0	-	4	5	-	Р	Е	
Pedicle screw kit 2x(06.0 x 40 mm)  S C - 6 0 - 4 0 - P E Pedicle screw kit 2x(06.0 x 45 mm)  S C - 6 0 - 4 5 - P E Pedicle screw kit 2x(06.0 x 50 mm)  S C - 6 0 - 5 0 - P E Pedicle screw kit 2x(06.0 x 50 mm)  S C - 6 0 - 5 5 0 - P E Pedicle screw kit 2x(06.0 x 50 mm)  S C - 6 0 - 5 5 5 - P E Pedicle screw kit 2x(07.0 x 35 mm)  S C - 7 0 - 3 5 5 - P E Pedicle screw kit 2x(07.0 x 40 mm)  S C - 7 0 - 4 0 - P E Pedicle screw kit 2x(07.0 x 45 mm)  S C - 7 0 - 4 5 - P E Pedicle screw kit 2x(07.0 x 45 mm)  S C - 7 0 - 4 5 - P E Pedicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 0 - P E Pedicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 - P E Pedicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 0 - P E Pedicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 5 - P E Redicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 5 - P E Redicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 5 - P E Redicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 5 - P E Redicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 0 - P E Redicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 0 - P E Redicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 0 - P E Redicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 0 - P E Redicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 0 - P E Redicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 0 - P E Redicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 0 - P E Redicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 0 - P E Redicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 0 - P E Redicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 0 - P E Redicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 0 - P E Redicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 0 - P E Redicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 0 - P E Redicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 0 - P E Redicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 0 - P E Redicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 0 - P E Redicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 0 - P E Redicle screw kit 2x(07.0 x 50 mm)  S C - 7 0 - 5 5 0 - P E Redicle screw kit 2x(0	Pedicle screw kit 2x (Ø5.0 x 50 mm)	S	С	-	5	0	-	5	0	-	Р	Е	
Pedicle screw kit 2x (06.0 x 45mm)	Pedicle screw kit 2 x (Ø6.0 x 35 mm)	S	С	-	6	0	-	3	5	-	Р	Е	
Pedicle screw kit 2 x (Ø60 x 50 mm)   S	Pedicle screw kit 2 x (Ø6.0 x 40 mm)	S	С	-	6	0	-	4	0	-	Р	Е	
Pedicle screw kit 2 x (Ø60 x 55 mm)	Pedicle screw kit 2 x (Ø6.0 x 45 mm)	S	С	-	6	0	-	4	5	-	Р	Е	
Pedicle screw kit 2 x (Ø7.0 x 35 mm)         S         C         -         7         0         -         3         5         -         P         E           Pedicle screw kit 2 x (Ø7.0 x 45 mm)         S         C         -         7         0         -         4         0         -         P         E           Pedicle screw kit 2 x (Ø7.0 x 50 mm)         S         C         -         7         0         -         5         0         -         P         E           Pedicle screw kit 2 x (Ø7.0 x 50 mm)         S         C         -         7         0         -         5         0         -         P         E           Pedicle screw kit 2 x (Ø7.0 x 50 mm)         S         C         -         7         0         -         5         0         -         P         E           Pedicle screw kit 2 x (Ø7.0 x 50 mm)         S         C         -         7         0         -         5         0         -         P         E           Pedicle screw kit 2 x (Ø7.0 x 50 mm)         S         C         -         7         0         -         6         0         -         8         0         -         0         0         -	Pedicle screw kit 2 x (Ø6.0 x 50 mm)	S	С	-	6	0	-	5	0	-	Р	Е	
Pedicle screw kit 2 x (Ø7.0 x 40 mm)         S         C         -         7         0         -         4         0         -         P         E           Pedicle screw kit 2 x (Ø7.0 x 45 mm)         S         C         -         7         0         -         4         5         -         P         E           Pedicle screw kit 2 x (Ø7.0 x 55 mm)         S         C         -         7         0         -         5         0         -         P         E           Pedicle screw instrument kit         S         I         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         4         0         -         P         E         E         0         0         0         -         4         0         -         P         B         B         0         -         0         0         -         4         0         -         P         B         B         0         -         0         0         -         5         0         -         P	Pedicle screw kit 2 x (Ø6.0 x 55 mm)	S	С	-	6	0	-	5	5	-	Р	Е	
Pedicle screw kit 2x(Ø7.0 x 45 mm)         S         C         -         7         0         -         4         5         -         P         E           Pedicle screw kit 2x(Ø7.0 x 50 mm)         S         C         -         7         0         -         5         0         -         P         E           Pedicle screw kit 2x(Ø7.0 x 55 mm)         S         C         -         7         0         -         5         5         -         P         E           Pedicle screw kit 2x(Ø7.0 x 55 mm)         S         C         -         7         0         -         5         5         -         P         E           Pedicle screw kit 2x(Ø7.0 x 55 mm)         S         C         -         7         0         -         5         0         -         8         B         0         0         0         -         0         0         -         0         0         -         7         0         -	Pedicle screw kit 2 x (Ø7.0 x 35 mm)	S	С	-	7	0	-	3	5	-	Р	Е	
Pedicle screw kit 2x(Ø7.0 x 50 mm)         S         C         -         7         0         -         5         0         -         P         E           Pedicle screw kit 2x(Ø7.0 x 55 mm)         S         C         -         7         0         -         5         5         -         P         E           Pedicle screw kit 2x(Ø7.0 x 55 mm)         S         C         -         7         0         -         5         5         -         P         E           Pedicle screw kit 2x(Ø7.0 x 55 mm)         S         C         -         7         0         -         5         5         -         P         E           Pedicle screw kit 2x(Ø7.0 x 55 mm)         R         D         0         0         -         0         0         -         0         0         0         -         8         D         -         0         0         -         6         0         -         8         B         -         0         0         -         6         0         -         P         B         8         0         -         0         0         -         7         0         -         P         B         0         -	Pedicle screw kit 2x (Ø7.0 x 40 mm)	S	С	-	7	0	-	4	0	-	Р	Е	
Pedicle screw kit 2 x (Ø7.0 x 55mm)         S         C         -         7         0         -         5         5         -         P         E           Pedicle screw instrument kit         S         I         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         8         B         B         B         0         -         0         0         -         4         0         -         P         B         B         0         -         0         0         -         5         0         -         P         B         B         0         0         0         -         5         0         -         P         B         B         0         0         0         -         6         0         -         P         B         B         0         0         0         -         7         0         -         8 <td>Pedicle screw kit 2x (Ø7.0 x 45 mm)</td> <td>S</td> <td>С</td> <td>-</td> <td>7</td> <td>0</td> <td>-</td> <td>4</td> <td>5</td> <td>-</td> <td>Р</td> <td>Е</td>	Pedicle screw kit 2x (Ø7.0 x 45 mm)	S	С	-	7	0	-	4	5	-	Р	Е	
Pedicle screw instrument kit         S         I         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         S         B           Rod kit S1/L5 40 mm (2x)         R         D         -         0         0         -         4         0         -         S         B           Rod kit S1/L5 40 mm (2x)         R         D         -         0         0         -         4         0         -         S         B           Rod kit S1/L5 40 mm (2x)         R         D         -         0         0         -         4         0         -         P         B           Rod kit straight 50 mm (2x)         R         D         -         0         0         -         6         0         -         P         B           Rod kit straight 30 mm (2x)         R         D         -         0         0         -         3         0         -         S         T           Rod kit straight 30 mm (2x)         R         D         -         0         0         -         6         0         -         S	Pedicle screw kit 2x (Ø7.0 x 50 mm)	S	С	-	7	0	-	5	0	-	Р	Е	
Rod kit S1/L5 30 mm (2x)         R         D         -         0         0         -         3         0         -         S         B           Rod kit S1/L5 40 mm (2x)         R         D         -         0         0         -         4         0         -         S         B           Rod kit pre-bent 40 mm (2x)         R         D         -         0         0         -         4         0         -         P         B           Rod kit pre-bent 50 mm (2x)         R         D         -         0         0         -         6         0         -         P         B           Rod kit pre-bent 60 mm (2x)         R         D         -         0         0         -         6         0         -         P         B           Rod kit pre-bent 70 mm (2x)         R         D         -         0         0         -         6         0         -         P         B           Rod kit straight 30 mm (2x)         R         D         -         0         0         -         6         0         -         S         T           Rod kit straight 80 mm (2x)         R         D         -         0         <	Pedicle screw kit 2x (Ø7.0 x 55 mm)	S	С	-	7	0	-	5	5	-	Р	Е	
Rod kit S1/L5 40 mm (2x)         R         D         -         0         0         -         4         0         -         S         B           Rod kit pre-bent 40 mm (2x)         R         D         -         0         0         -         4         0         -         P         B           Rod kit pre-bent 50 mm (2x)         R         D         -         0         0         -         5         0         -         P         B           Rod kit pre-bent 60 mm (2x)         R         D         -         0         0         -         6         0         -         P         B           Rod kit pre-bent 70 mm (2x)         R         D         -         0         0         -         6         0         -         P         B           Rod kit pre-bent 70 mm (2x)         R         D         -         0         0         -         6         0         -         P         B           Rod kit straight 30 mm (2x)         R         D         -         0         0         -         8         0         -         S         T           Rod kit straight 80 mm (2x)         R         D         -         0	Pedicle screw instrument kit	S	1	-	0	0	-	0	0	-	0	0	
Rod kit pre-bent 40 mm (2x)         R         D         -         0         0         -         4         0         -         P         B           Rod kit pre-bent 50 mm (2x)         R         D         -         0         0         -         5         0         -         P         B           Rod kit pre-bent 60 mm (2x)         R         D         -         0         0         -         6         0         -         P         B           Rod kit pre-bent 70 mm (2x)         R         D         -         0         0         -         6         0         -         P         B           Rod kit pre-bent 70 mm (2x)         R         D         -         0         0         -         7         0         -         P         B           Rod kit straight 30 mm (2x)         R         D         -         0         0         -         6         0         -         S         T           Rod kit straight 80 mm (2x)         R         D         -         0         0         -         8         0         -         S         T           Rod kit straight 80 mm (2x)         R         D         -         0	Rod kit S1/L5 30 mm (2x)	R	D	-	0	0	-	3	0	-	S	В	
Rod kit pre-bent 50 mm (2x)         R         D         -         0         0         -         5         0         -         P         B           Rod kit pre-bent 60 mm (2x)         R         D         -         0         0         -         6         0         -         P         B           Rod kit pre-bent 70 mm (2x)         R         D         -         0         0         -         7         0         -         P         B           Rod kit pre-bent 70 mm (2x)         R         D         -         0         0         -         7         0         -         P         B           Rod kit pre-bent 70 mm (2x)         R         D         -         0         0         -         3         0         -         S         T           Rod kit straight 30 mm (2x)         R         D         -         0         0         -         8         0         -         S         T           Rod kit straight 80 mm (2x)         R         D         -         0         0         -         8         0         -         S         T           Rod kit straight 90 mm (2x)         R         D         -         0	Rod kit S1/L5 40 mm (2x)	R	D	-	0	0	-	4	0	-	S	В	
Rod kit pre-bent 60 mm (2x)         R         D         -         0         0         -         6         0         -         P         B           Rod kit pre-bent 70 mm (2x)         R         D         -         0         0         -         7         0         -         P         B           Rod kit straight 30 mm (2x)         R         D         -         0         0         -         3         0         -         S         T           Rod kit straight 60 mm (2x)         R         D         -         0         0         -         6         0         -         S         T           Rod kit straight 70 mm (2x)         R         D         -         0         0         -         7         0         -         S         T           Rod kit straight 80 mm (2x)         R         D         -         0         0         -         8         0         -         S         T           Rod kit straight 90 mm (2x)         R         D         -         0         0         -         9         0         -         S         T           Rod kit straight 90 mm (2x)         R         D         -         0	Rod kit pre-bent 40 mm (2x)	R	D	-	0	0	-	4	0	-	Р	В	
Rod kit pre-bent 70 mm (2x)         R         D         -         0         0         -         7         0         -         P         B           Rod kit straight 30 mm (2x)         R         D         -         0         0         -         3         0         -         S         T           Rod kit straight 60 mm (2x)         R         D         -         0         0         -         6         0         -         S         T           Rod kit straight 70 mm (2x)         R         D         -         0         0         -         8         0         -         S         T           Rod kit straight 80 mm (2x)         R         D         -         0         0         -         8         0         -         S         T           Rod kit straight 90 mm (2x)         R         D         -         0         0         -         9         0         -         S         T           Rod kit straight 90 mm (2x)         R         D         -         0         1         -         0         0         -         S         T           Compressor distractor kit         C         D         -         0	Rod kit pre-bent 50 mm (2x)	R	D	-	0	0	-	5	0	-	Р	В	
Rod kit straight 30 mm (2x)       R       D       -       0       0       -       3       0       -       S       T         Rod kit straight 60 mm (2x)       R       D       -       0       0       -       6       0       -       S       T         Rod kit straight 70 mm (2x)       R       D       -       0       0       -       8       0       -       S       T         Rod kit straight 80 mm (2x)       R       D       -       0       0       -       8       0       -       S       T         Rod kit straight 90 mm (2x)       R       D       -       0       0       -       9       0       -       S       T         Rod kit straight 90 mm (2x)       R       D       -       0       0       -       9       0       -       S       T         Rod kit straight 90 mm (2x)       R       D       -       0       1       -       0       0       -       S       T         Rod kit straight 90 mm (2x)       R       D       -       0       1       -       0       0       -       S       T         Compressor distractor k	Rod kit pre-bent 60 mm (2x)	R	D	-	0	0	-	6	0	-	Р	В	
Rod kit straight 60 mm (2x)         R         D         -         0         0         -         6         0         -         S         T           Rod kit straight 70 mm (2x)         R         D         -         0         0         -         7         0         -         S         T           Rod kit straight 80 mm (2x)         R         D         -         0         0         -         8         0         -         S         T           Rod kit straight 90 mm (2x)         R         D         -         0         0         -         9         0         -         S         T           Rod kit straight 100 mm (2x)         R         D         -         0         1         -         0         0         -         S         T           Rod kit straight 100 mm (2x)         R         D         -         0         1         -         0         0         -         S         T           Compressor distractor kit         C         D         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         - <t< td=""><td>Rod kit pre-bent 70 mm (2x)</td><td>R</td><td>D</td><td>-</td><td>0</td><td>0</td><td>-</td><td>7</td><td>0</td><td>-</td><td>Р</td><td>В</td></t<>	Rod kit pre-bent 70 mm (2x)	R	D	-	0	0	-	7	0	-	Р	В	
Rod kit straight 70 mm (2x)         R         D         -         0         0         -         7         0         -         S         T           Rod kit straight 80 mm (2x)         R         D         -         0         0         -         8         0         -         S         T           Rod kit straight 90 mm (2x)         R         D         -         0         0         -         9         0         -         S         T           Rod kit straight 90 mm (2x)         R         D         -         0         0         -         9         0         -         S         T           Rod kit straight 100 mm (2x)         R         D         -         0         1         -         0         0         -         S         T           Compressor distractor kit         C         D         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -	Rod kit straight 30 mm (2x)	R	D	-	0	0	-	3	0	-	S	Т	
Rod kit straight 80 mm (2x)       R       D       -       0       0       -       8       0       -       S       T         Rod kit straight 90 mm (2x)       R       D       -       0       0       -       9       0       -       S       T         Rod kit straight 100 mm (2x)       R       D       -       0       1       -       0       0       -       S       T         Compressor distractor kit       C       D       -       0       0       -       0       0       -       0       0         Cement pusher 1 cc (10xCP-01-00-01)       C       P       -       0       1       -       0       0       -       0       0         Cement pusher 1cc       C       P       -       0       1       -       0       0       -       0       0         Removal kit       R       E       -       0       0       -       0       0       -       0       0       -       0       0       0       0       0       0       0       0       0       0       0       0       0       0       0       0       0       0 <td>Rod kit straight 60 mm (2x)</td> <td>R</td> <td>D</td> <td>-</td> <td>0</td> <td>0</td> <td>-</td> <td>6</td> <td>0</td> <td>-</td> <td>S</td> <td>Т</td>	Rod kit straight 60 mm (2x)	R	D	-	0	0	-	6	0	-	S	Т	
Rod kit straight 90 mm (2x)         R         D         -         0         0         -         9         0         -         S         T           Rod kit straight 100 mm (2x)         R         D         -         0         1         -         0         0         -         S         T           Compressor distractor kit         C         D         -         0         0         -         0         0         -         0         0           Cement pusher 1 cc (10xCP-01-00-01)         C         P         -         0         1         -         0         0         -         0         0           Cement pusher 1 cc (10xCP-01-00-01)         C         P         -         0         1         -         0         0         -         0         0           Removal kit         R         E         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -	Rod kit straight 70 mm (2x)	R	D	-	0	0	-	7	0	-	S	Т	
Rod kit straight 100 mm (2x)       R       D       -       0       1       -       0       0       -       S       T         Compressor distractor kit       C       D       -       0       0       -       0       0       -       0       0         Cement pusher 1 cc       C       P       -       0       1       -       0       0       -       0       0         Cement pusher 1 cc       C       P       -       0       1       -       0       0       -       0       0         Cement pusher 1 cc       C       P       -       0       1       -       0       0       -       0       0         Cement pusher 1 cc       C       P       -       0       1       -       0       0       -       0       0       -       0       0       -       0       0       -       0       0       -       0       0       -       0       0       -       0       0       -       0       0       -       0       0       -       0       0       -       0       0       -       0       0       - <td< td=""><td>Rod kit straight 80 mm (2x)</td><td>R</td><td>D</td><td>-</td><td>0</td><td>0</td><td>-</td><td>8</td><td>0</td><td>-</td><td>S</td><td>Т</td></td<>	Rod kit straight 80 mm (2x)	R	D	-	0	0	-	8	0	-	S	Т	
Compressor distractor kit  C D - 0 0 - 0 0 - 0 0  Cement pusher 1 cc (10xCP-01-00-01)  C P - 0 1 - 0 0 - 0 0  Cement pusher 1cc  C P - 0 1 - 0 0 - 0 0  Removal kit  R E - 0 0 - 0 0 - 0 0  Screw driver Kit  S D - 0 0 - 0 0 - 0 0  1.5mm K-wire (5xKW-00-00-01)  K W - 0 0 - 0 0 - 0 0  1.5mm K-wire (1x2)  K W - 0 0 - 0 0 - 0 1  Tap kit diameter 5.0  T P - 5 0 - 0 0 - 0 0  Tap kit diameter 7.0  T P - 7 0 - 0 0 - 0 0  Surgical technique (English)	Rod kit straight 90 mm (2x)	R	D	-	0	0	-	9	0	-	S	Т	
Cement pusher 1 cc (10xCP-01-00-01)         C         P         -         0         1         -         0         0         -         0         0           Cement pusher 1cc         C         P         -         0         1         -         0         0         -         0         1           Removal kit         R         E         -         0         0         -         0         0         -         0         0           Screw driver Kit         S         D         -         0         0         -         0         0         -         0         0           1.5mm K-wire (5xKW-00-00-01)         K         W         -         0         0         -         0         0         -         0         0           1.5mm K-wire (1x2)         K         W         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0         -         0         0 <td>Rod kit straight 100 mm (2x)</td> <td>R</td> <td>D</td> <td>-</td> <td>0</td> <td>1</td> <td>-</td> <td>0</td> <td>0</td> <td>-</td> <td>S</td> <td>Т</td>	Rod kit straight 100 mm (2x)	R	D	-	0	1	-	0	0	-	S	Т	
Cement pusher 1cc         C         P         -         0         1         -         0         0         -         0         1           Removal kit         R         E         -         0         0<	Compressor distractor kit	С	D	-	0	0	-	0	0	-	0	0	
Removal kit       R       E       -       0       0       -       0       0       -       0       0         Screw driver Kit       S       D       -       0       0       -       0       0       -       0       0         1.5mm K-wire (5xKW-00-00-01)       K       W       -       0       0       -       0       0       -       0       0         1.5mm K-wire (1x2)       K       W       -       0       0       -       0       0       -       0       0         Tap kit diameter 5.0       T       P       -       5       0       -       0       0       -       0       0         Tap kit diameter 6.0       T       P       -       6       0       -       0       0       -       0       0         Tap kit diameter 7.0       T       P       -       7       0       -       0       0       -       0       0         Surgical technique (English)       S       T       -       P       S       -       0       E       -       N       G	Cement pusher 1 cc (10xCP-01-00-01)	С	Р	-	0	1	-	0	0	-	0	0	
Screw driver Kit         S         D         -         0         0         -         0         0         -         0         0           1.5mm K-wire (5xKW-00-00-01)         K         W         -         0         0         -         0         0         -         0         0           1.5mm K-wire (1x2)         K         W         -         0         0	Cement pusher 1cc	С	Р	-	0	1	-	0	0	-	0	1	
1.5mm K-wire (5xKW-00-00-01)       K       W       -       0       0       -       0       0       -       0       0         1.5mm K-wire (1x2)       K       W       -       0       0       -       0       0       -       0       1         Tap kit diameter 5.0       T       P       -       5       0       -       0       0       -       0       0         Tap kit diameter 6.0       T       P       -       6       0       -       0       0       -       0       0         Tap kit diameter 7.0       T       P       -       7       0       -       0       0       -       0       0         Surgical technique (English)       S       T       -       P       S       -       0       E       -       N       G	Removal kit	R	Е	-	0	0	-	0	0	-	0	0	
1.5mm K-wire (1x2)       K       W       -       0       0       -       0       0       -       0       1         Tap kit diameter 5.0       T       P       -       5       0       -       0       0       -       0       0         Tap kit diameter 6.0       T       P       -       6       0       -       0       0       -       0       0         Tap kit diameter 7.0       T       P       -       7       0       -       0       0       -       0       0         Surgical technique (English)       S       T       -       P       S       -       0       E       -       N       G	Screw driver Kit	S	D	-	0	0	-	0	0	-	0	0	
Tap kit diameter 5.0       T       P       -       5       0       -       0       0       -       0       0         Tap kit diameter 6.0       T       P       -       6       0       -       0       0       -       0       0         Tap kit diameter 7.0       T       P       -       7       0       -       0       0       -       0       0         Surgical technique (English)       S       T       -       P       S       -       0       E       -       N       G	1.5mm K-wire (5xKW-00-00-01)	K	W	-	0	0	-	0	0	-	0	0	
Tap kit diameter 6.0	1.5mm K-wire (1x2)	K	W	-	0	0	-	0	0	-	0	1	
Tap kit diameter 7.0       T       P       -       7       0       -       0       0       -       0       0         Surgical technique (English)       S       T       -       P       S       -       0       E       -       N       G	Tap kit diameter 5.0	Т	Р	-	5	0	-	0	0	-	0	0	
Surgical technique (English)  S T - P S - 0 E - N G	Tap kit diameter 6.0	Т	Р	-	6	0	-	0	0	-	0	0	
	Tap kit diameter 7.0	Т	Р	-	7	0	-	0	0	-	0	0	
IFU (English) I F - U P - S E - N G	Surgical technique (English)	S	Т	-	Р	S	-	0	Е	-	N	G	
	IFU (English)	1	F	-	U	Р	-	S	Е	-	N	G	

## **CONTACT**

NEO MEDICAL SA HQ POSTAL ADDRESS

Route de Lausanne 157a 1096 Villette Switzerland

+41 22 548 38 80

info@neo-medical.com www.neo-medical.com

NEO MEDICAL CUSTOMER SERVICE AUSTRALIA (Point Blank Medical) 1300 001 726 (PBM)

sales@ pointblankmedical.com

NEO MEDICAL CUSTOMER SERVICE INTERNATIONAL

+49-7333 925 998 90

NEO MEDICAL CUSTOMER SERVICE GERMANY

+49-7333 925 998 90

NEO MEDICAL CUSTOMER SERVICE FRANCE

+33-480 92 23 22

info.france @neo-medical.com